

# Hair coloration

Present it successfully  
with dynamic **POS<sub>T</sub>** - Solutions



For a successful presentation of hair coloration:


**POS T-Push Feed 6 N**  
B 40, Front F, 39 x 25 mm

Art. pvpc6800




**Divider, System F**  
H 60 mm

Art. d06fc...



**Adapter-T-Rail**  
for fixation of Pusher-Systems and Dividers  
(s. page 2)



**Accessories**  
**Labelholder**  
B 49 x H 80 mm













Art. e49t0080




References +  
Solutions

# Installation

## 1. Equipping shelves with Adapter-T-Rails

Rail	Design	Description	Appliance	Article	Mounting Adapter-T-Rail
a03		Adaptor-T-Rail 03, W 21 mm, selfadhesive	Metal, glass, wood, plastic	a03s0648 65 mm shelf a03s0995 100 mm shelf a03s1245 12 mm shelf	
a04		Adaptor-T-Rail 04, W 13 mm, splay 8 mm, selfadhesive	Glass, height 8 mm	a04s0648 65 mm shelf a04s0995 100 mm shelf a04s1245 125 mm shelf	
a10		Adaptor-T-Rail 10, W 21 mm, for wire shelves	Wire shelves (3 Clips 11631 needed)	a10x0590 65 mm shelf a10x0990 100 mm shelf a10x1240 125 mm shelf	
a13		Adaptor T-Rail13, for double wire shelves	Shelves with double wire front	a13x0646 65 mm shelf a13x0980 100 mm shelf a13x1230 125 mm shelf	
a15		Adaptor-T-Rail 15 for U-bead	Metal shelves with U-Bead in front	a15x0638 65 mm shelf a15x0988 100 mm shelf a15x1238 125 mm shelf	
a26		Adaptor-T-Rail 26, W 18 mm, with adaptor for scanner profile	Shelves with double wire front	a26x0630 65 mm shelf a26x0980 100 mm shelf a26x1230 12 mm shelf	

## 2. Installation adapter profile, push feed and divider for hair coloration



1. Mount Adapter-T-Rail at shelf front
  - please clean the surface before installation
2. Clip Frontstop of Compartment-Pusher onto Adapter-T-Rail. Install additional Compartments according to product widths.
3. Fix the Push Feed in the middle. Clip the Push Feed onto the Adapter-T-Rail.
4. Pin up the label holder and insert the label-cards.

\*(Dimensions of Adapter-T-Rail depend on product type and dimensions)

These and many more can be delivered in all sizes – for additional Adaptor- and Scanner-Rails and please see „POS T-Adaptor-Rails“.